

# P64AXR/1.0

P64AXR c/w 4 Core 0.75mm<sup>2</sup> 1m PVC Lead



- Main electrical features
  - Rated operational voltage  $U_e$   
207 / 230 / 253 V
  - Rated current  
6 A
- Materials
  - Colour  
red
- Connection
  - Cable End  
Prepared - end of barrel closed
- Cable
  - Conductor Size  
0.75 mm<sup>2</sup>
  - Cable Material  
PVC
  - Cable length  
1000 mm
- Equipment
  - Number of terminations -plugs  
4
  - Contact Material  
Phosphor Bronze
- Use
  - Mechanical Load  
5 Kg maximum
- Safety

- Inflammability  
UL 94 V0
- Identification
  - Application, usage  
Light control