

P64AXR/LSF/1.0

P64AXR c/w 4 Core 0.75mm² 1m LS0H Lead

Main electrical features

Rated operational voltage Ue 207 / 230 / 253 V

Rated current 6 A

Materials

Colour red

Connection

Cable End Prepared - end of barrel closed

Cable

Conductor Size 0.75 mm²

Cable Material Low Smoke Zero Halogen

Cable length 1000 mm

Equipment

Number of terminations -plugs 4

Contact Material Phosphor Bronze

Use

Mechanical Load 5 Kg maximum

Safety

Inflammability UL 94 V0

Identification

Application, usage Light control
