

Product data sheet

P64AXR/1.0LSF/3

:hager



P64AXR c/w 4 Core 1.00mm² 3m LS0H Lead

Technical Characteristics

	207 V
	230 V
Rated operational voltage U _e	253 V
Rated current	6 A
Colour	red
Cable End	Prepared - end of barrel closed
Conductor Size	1 mm ²
Cable Material	Low Smoke Zero Halogen
Number of terminations -plugs	4
Contact Material	Phosphor Bronze
Mechanical Load	5 Kg maximum
Inflammability	UL 94 V0
Application, usage	Light control