

Product data sheet

P64AXR/1.0

:hager



P64AXR c/w 4 Core 0.75mm² 1m PVC Lead

Technical Characteristics

	230 V
	253 V
Rated operational voltage U _e	207 V
Rated current	6 A
Colour	red
Cable End	Prepared - end of barrel closed
Conductor Size	0.75 mm ²
Cable Material	PVC
Number of terminations -plugs	4
Contact Material	Phosphor Bronze
Mechanical Load	5 Kg maximum
Inflammability	UL 94 V0
Application, usage	Light control