

SM101C

Communicant Modular multifunction meter



Architecture

Fixing mode	Din-Rail
-------------	----------

Main electrical features

Rated operational voltage Ue	200 / 230 / 277 V
Frequency	50;60 Hz

Voltage

Supply voltage	230V +10 ; -15%
----------------	-----------------

Dimensions

Depth of installed product	50 mm
Height of installed product	45 mm
Length	67 mm
Width of installed product	73 mm

Power

Power consumed	5 VA
Total power loss under IN	5 W

Technical characteristics SM101C

Measurement

Type of measuring instrument multimeter

Capacity

Number of modules 4

Installation, mounting

Mounting type din-Rail

Connection

Connection cross-sect. flexible conductor 0,5 ; 4mm²

Connection cross-sect. rigid cable 0,5 ; 4mm²

Type of connection with screw

Equipment

Type of display Digital

Safety

Protection index IP IP20

Use conditions

Storage temperature -20/70 °C

Temperature

Operating temperature -10/55 °C
