

# Product data sheet

P64AX/LSF/1.0

**:hager**



## P64AX c/w 4 Core 0.75mm<sup>2</sup> 1m LSOH Lead

### Technical Characteristics

	230 V
	253 V
Rated operational voltage U <sub>e</sub>	207 V
Rated current	6 A
Colour	pure white
Cable End	Prepared - end of barrel closed
Cable Material	Low Smoke Zero Halogen
Number of terminations -plugs	4
Contact Material	Phosphor Bronze
Mechanical Load	5 Kg maximum
Inflammability	UL 94 V0
Application, usage	Light control