

WMS51

5A 1 Gang Unswitched Socket

Architecture

| | |
|-------------|----------------|
| Fixing mode | flush-mounting |
|-------------|----------------|

Main electrical features

| | |
|-----------------|-------|
| Nominal voltage | 250 V |
|-----------------|-------|

| | |
|---------------|--------------|
| Rated voltage | 220/230 V AC |
|---------------|--------------|

| | |
|---------------|-----|
| Rated current | 5 A |
|---------------|-----|

| | |
|---------------|-----|
| Rated current | 5 A |
|---------------|-----|

Dimensions

| | |
|-------|-------|
| Depth | 25 mm |
|-------|-------|

| | |
|--------|-------|
| Height | 86 mm |
|--------|-------|

| | |
|-------|-------|
| Width | 86 mm |
|-------|-------|

Frequency

| | |
|-----------|----------|
| Frequency | 50;60 Hz |
|-----------|----------|

Capacity

| | |
|-------------------|---|
| Number of modules | 0 |
|-------------------|---|

Cover, door

| | |
|-------|------------------|
| Cover | Full cover plate |
|-------|------------------|

Materials

| | |
|--------|-------|
| Colour | white |
|--------|-------|

| | |
|----------|-------------------|
| Material | Urea-formaldehyde |
|----------|-------------------|

| | |
|--------------------|--------|
| Surface appearance | glossy |
|--------------------|--------|

| | |
|---------------------------|-----------|
| Type of surface treatment | untreated |
|---------------------------|-----------|

| | |
|-----------------------|-------|
| Colour syntax: Colour | white |
|-----------------------|-------|

Installation, mounting

| | |
|---------|-----------------|
| Imprint | without imprint |
|---------|-----------------|

Connection

| | |
|--------------------|-------|
| Type of connection | screw |
|--------------------|-------|

Cable

| | |
|--------|-----------------------|
| Wiring | with earth connection |
|--------|-----------------------|

Scope of delivery

| | |
|-----------|-----------------------------------|
| Component | with 2 fixing screws M3.5 x 30 mm |
|-----------|-----------------------------------|

Safety

| | |
|---------------------|------|
| Protection index IP | IP20 |
|---------------------|------|

| | |
|------------|-----------------------------|
| Protection | Enhanced contact protection |
|------------|-----------------------------|

Identification

| | |
|---|--|
| Designation syntax: Core designation/function socket outlet | |
|---|--|
