

# WMSS81RR

## 1 Gang Double Pole Switched Socket with Red Face Plate & Rocker

### Architecture

Fixing mode	flush-mounting
-------------	----------------

### Main electrical features

Nominal voltage	250 V
Rated voltage	220/230 V AC
Rated current	13 A
Rated current	13 A

### Dimensions

Depth	25.8 mm
Height	86 mm
Width	86 mm

### Frequency

Frequency	50;60 Hz
-----------	----------

### Capacity

Number of modules	0
-------------------	---

---

Cover, door

Cover	Full cover plate
-------	------------------

---

Materials

Colour	red
--------	-----

---

Material	duroplastic
----------	-------------

---

Surface appearance	glossy
--------------------	--------

---

Type of surface treatment	untreated
---------------------------	-----------

---

Colour syntax: Colour	red
-----------------------	-----

---

Installation, mounting

Imprint	without imprint
---------	-----------------

---

Connection

Type of connection	screw
--------------------	-------

---

Cable

Wiring	with earth connection
--------	-----------------------

---

Scope of delivery

Component	with 2 fixing screws M3.5 x 30 mm
-----------	-----------------------------------

---

Safety

Protection index IP	IP20
---------------------	------

---

Protection	Enhanced contact protection
------------	-----------------------------

---

Identification

Designation syntax: Core designation/function socket outlet	
---	--

---