

EE905

Control 60 emergency lights



- Main electrical features
 - Frequency
50 Hz
- Dimensions
 - Depth of installed product
65 mm
 - Height of installed product
85 mm
 - Length
65 mm
 - Width of installed product
70 mm
- Power
 - Total power loss under IN
3 W
 - Power dissipation per coil
0.8 W
- Capacity
 - Number of modules
4
- Materials
 - Material
plastic
- Connection
 - Connection cross-sect. flexible conductor
1 / 6mm²
 - Connection cross-sect. rigid cable

1,5 / 10mm²

- Safety
 - Protection index IP
IP20
- Use conditions
 - Storage temperature
-20/80 °C
- Temperature
 - Operating temperature
-10/40 °C