

WMSS82OR

2 Gang Double Pole Switched Socket Dual Earth Outboard Red Rockers

Architecture

Fixing mode	flush-mounting
-------------	----------------

Main electrical features

Nominal voltage	250 V
Rated voltage	220/230 V AC
Rated current	13 A
Rated current	13 A

Dimensions

Depth	29.5 mm
Height	86 mm
Width	146 mm

Frequency

Frequency	50;60 Hz
-----------	----------

Capacity

Number of modules	0
-------------------	---

Cover, door

Cover	Full cover plate
-------	------------------

Materials

Colour	white
--------	-------

Material	Urea-formaldehyde
----------	-------------------

Surface appearance	glossy
--------------------	--------

Type of surface treatment	untreated
---------------------------	-----------

Colour syntax: Colour	white
-----------------------	-------

Installation, mounting

Imprint	without imprint
---------	-----------------

Connection

Type of connection	screw
--------------------	-------

Cable

Wiring	with double earth connection
--------	------------------------------

Scope of delivery

Component	with 2 fixing screws M3.5 x 30 mm
-----------	-----------------------------------

Safety

Protection index IP	IP20
---------------------	------

Protection	Enhanced contact protection
------------	-----------------------------

Identification

Designation syntax: Core designation/function socket outlet	
---	--
