

# WPSS81B

## 1 Gang Double Pole Switched Socket & Back Box without Knockouts

### Architecture

Fixing mode	surface-mounting
-------------	------------------

### Main electrical features

Nominal voltage	250 V
-----------------	-------

Rated voltage	220/230 V AC
---------------	--------------

Rated current	13 A
---------------	------

Rated current	13 A
---------------	------

### Dimensions

Depth	53.2 mm
-------	---------

Height	86 mm
--------	-------

Width	86 mm
-------	-------

### Frequency

Frequency	50;60 Hz
-----------	----------

### Capacity

Number of modules	0
-------------------	---

---

Cover, door

**Cover** Full cover plate

---

Materials

**Colour** grey

---

**Material** Steel

---

**Surface appearance** glossy

---

**Type of surface treatment** Epoxy

---

**Colour syntax: Colour** grey

---

Installation, mounting

**Imprint** without imprint

---

Connection

**Type of connection** screw

---

Cable

**Wiring** with earth connection

---

Scope of delivery

**Component** with 2 fixing screws M3.5 x 20 mm and M3.5 x 30 mm each

---

Safety

**Protection index IP** IP20

---

**Protection** Enhanced contact protection

---

Identification

**Designation syntax: Core designation/function socket outlet**

---