

WPSS81N

1 Gang Double Pole Switched Socket with LED Indicator

Architecture

| | |
|-------------|------------------|
| Fixing mode | surface-mounting |
|-------------|------------------|

Main electrical features

| | |
|-----------------|-------|
| Nominal voltage | 250 V |
|-----------------|-------|

| | |
|---------------|--------------|
| Rated voltage | 220/230 V AC |
|---------------|--------------|

| | |
|---------------|------|
| Rated current | 13 A |
|---------------|------|

| | |
|---------------|------|
| Rated current | 13 A |
|---------------|------|

Dimensions

| | |
|-------|-------|
| Depth | 26 mm |
|-------|-------|

| | |
|--------|-------|
| Height | 86 mm |
|--------|-------|

| | |
|-------|-------|
| Width | 86 mm |
|-------|-------|

Frequency

| | |
|-----------|----------|
| Frequency | 50;60 Hz |
|-----------|----------|

Capacity

| | |
|-------------------|---|
| Number of modules | 0 |
|-------------------|---|

Cover, door

Cover Full cover plate

Materials

Colour grey

Material Steel

Surface appearance glossy

Type of surface treatment Epoxy

Colour syntax: Colour grey

Installation, mounting

Imprint without imprint

Connection

Type of connection screw

Cable

Wiring with earth connection

Scope of delivery

Component with 2 fixing screws M3.5 x 20 mm and M3.5 x 30 mm each

Safety

Protection index IP IP20

Protection Enhanced contact protection

Identification

Designation syntax: Core designation/function socket outlet
