

WPSS81NB

1 Gang Double Pole Switched Socket with LED Indicator & Back Box without Knockou



- Architecture
 - Fixing mode
surface-mounting
- Main electrical features
 - Nominal voltage
250 V
 - Rated voltage
220/230 V AC
 - Rated current
13 A
 - Rated current
13 A
- Dimensions
 - Depth
53.2 mm
 - Height
86 mm
 - Width
86 mm
- Frequency
 - Frequency
50;60 Hz
- Capacity
 - Number of modules
0
- Cover, door
 - Cover

- Full cover plate
- Materials
 - Colour
grey
 - Material
Steel
 - Surface appearance
glossy
 - Type of surface treatment
Epoxy
 - Colour syntax: Colour
grey
- Installation, mounting
 - Imprint
without imprint
- Connection
 - Type of connection
screw
- Cable
 - Wiring
with earth connection
- Scope of delivery
 - Component
with 2 fixing screws M3.5 x 20 mm and M3.5 x 30 mm each
- Safety
 - Protection index IP
IP20
 - Protection
Enhanced contact protection
- Identification
 - Designation syntax: Core designation/function
socket outlet