

WPSS82NBKO

2 Gang Double Pole Switched Socket with LED Indicator & Back Box with Knockouts

Architecture

Fixing mode	flush-mounting
-------------	----------------

Main electrical features

Nominal voltage	250 V
-----------------	-------

Rated voltage	220/230 V AC
---------------	--------------

Rated current	13 A
---------------	------

Rated current	13 A
---------------	------

Dimensions

Depth	53.2 mm
-------	---------

Height	86 mm
--------	-------

Width	146 mm
-------	--------

Frequency

Frequency	50;60 Hz
-----------	----------

Capacity

Number of modules	0
-------------------	---

Cover, door

Cover Full cover plate

Materials

Colour grey

Material Steel

Surface appearance glossy

Type of surface treatment Epoxy

Colour syntax: Colour grey

Installation, mounting

Imprint without imprint

Connection

Type of connection screw

Cable

Wiring with double earth connection

Scope of delivery

Component with 2 fixing screws M3.5 x 20 mm and M3.5 x 30 mm each

Safety

Protection index IP IP20

Protection Enhanced contact protection

Identification

Designation syntax: Core designation/function socket outlet
