

WXPS82

IP66 Twin 13A Un-switched Socket



- Architecture
 - Fixing mode
flush-mounting
- Main electrical features
 - Nominal voltage
250 V
 - Rated voltage
220/230 V AC
 - Rated current
13 A
 - Rated current
13 A
- Dimensions
 - Depth
88.25 mm
 - Height
116.5 mm
 - Width
146 mm
- Frequency
 - Frequency
50;60 Hz
- Capacity
 - Number of modules
0
- Cover, door
 - Cover

- Full cover plate
- Materials
 - Colour
light grey
 - Material
Polycarbonate (PC)
 - Surface appearance
glossy
 - Type of surface treatment
untreated
 - Colour syntax: Colour
light grey
- Installation, mounting
 - Imprint
without imprint
- Connection
 - Type of connection
screw
- Cable
 - Wiring
with double earth connection
- Safety
 - Protection index IP
IP66
 - Protection
Enhanced contact protection
- Identification
 - Designation syntax: Core designation/function
socket outlet