

WXPSS82

IP66 Twin 13A Double Pole Switched Socket



Architecture

Fixing mode	flush-mounting
-------------	----------------

Main electrical features

Nominal voltage	250 V
Rated voltage	220/230 V AC
Rated current	13 A

Dimensions

Depth	88.25 mm
Height	116.5 mm
Width	146 mm

Frequency

Frequency	50;60 Hz
-----------	----------

Capacity

Number of modules	0
-------------------	---

Cover, door

Cover	Full cover plate
-------	------------------

Materials

Colour	light grey
--------	------------

Material	Polycarbonate (PC)
----------	--------------------

Surface appearance	glossy
--------------------	--------

Type of surface treatment	untreated
---------------------------	-----------

Colour syntax: Colour	light grey
-----------------------	------------

Installation, mounting

Imprint	without imprint
---------	-----------------

Connection

Type of connection	screw
--------------------	-------

Cable

Wiring	with double earth connection
--------	------------------------------

Safety

Protection index IP	IP66
---------------------	------

Protection	Enhanced contact protection
------------	-----------------------------

Identification

Designation syntax: Core designation/function socket outlet
