



### RF external single push button wall mounted

#### Technical Characteristics

Number of keys	1
Fixing mode	surface-mounting
Function	easy additional functions: +6 scenes, on/off operating mode, 1 up/down button control configuration can simply be transferred from a master device reset function (to factory setting)
Operating voltage	3 V DC
Supply voltage	2 lithium batteries 3V CR2430
Height of installed product	76 mm
Width of installed product	49 mm
Max. transmission range	30m in house / 100m free field
Colour	polarwhite
RAL colour	RAL 9010 - Pure white
Mounting type	surface-mounted
Inscribable, with labelling field	No
Protection index IP	IP55
Operating temperature	-10 °C 55 °C