



### 6-fold radio push button silver with FPL

#### Technical Characteristics

Number of keys	3
Fixing mode	surface-mounting
Supply voltage	2 lithium batteries 3V CR2430
Depth of installed product	12 mm
Height of installed product	80.5 mm
Length	80.5 mm
Dimensions (LLxwwxhh)	80,5 x 80,5 x 12 mm
Width of installed product	80.5 mm
Max. transmission range	30m in house / 100m free field
Colour	silver
Inscribable, with labelling field	Yes
Number of channels	6
Protection index IP	IP30
Operating temperature	45 °C 0 °C