



4-fold radio push button white

Technical Characteristics

Number of keys	2
Fixing mode	surface-mounting
Supply voltage	2 lithium batteries 3V CR2430
Depth of installed product	12 mm
Height of installed product	80.5 mm
Length	80.5 mm
Dimensions (LLxwwxhh)	80,5 x 80,5 x 12 mm
Width of installed product	80.5 mm
Max. transmission range	30m in house / 100m free field
Colour	white
Inscribable, with labelling field	No
Number of channels	4
Protection index IP	IP30
Operating temperature	45 °C 0 °C