



Cell for twilight switch, wall mounted

Technical Characteristics

Fixing mode	surface-mounting
Depth of installed product	37 mm
Height of installed product	32 mm
Length	89 mm
Width of installed product	48 mm
Dimensions (W x H x D)	20 mm 25 mm
Maximum connection distance between receiver and transmitter	50m
Supply voltage	230 V +/- 10%
RAL colour	RAL 7035 - Light grey
Mounting type	surface-mounted
Protection index IP	IP54
Operating temperature	60 °C -30 °C