

MB2

Round Surface Box-30mm Deep



Voltage

Max operating voltage 240 V

Dimensions

Depth of installed product 31 mm

Height of installed product 85 mm

Width of installed product 85 mm

Materials

Colour pure white

Material PC;ABS

Safety

Inflammability UL 94 V0

Identification

Application, usage Light control