

49111

Weekly energy manager, 2 zones, comfort

:hager

- Main electrical features
 - Frequency
50 Hz
- Power
 - Power consumed
10 VA
- Capacity
 - Number of modules
3
- Power supply
 - Supply voltage
230 V AC
- Connection
 - Connection cross-sect. flexible conductor
1 / 4mm²
 - Connection cross-sect. rigid cable
1 / 4mm²
 - Number of contacts
4
- Settings
 - Shortest switching time
30 mn
- Scope of delivery
 - Contents of the kit
1 modular device + 1 ambient device
- Use
 - Cycle

weekly

- Safety
 - Protection index IP
IP30
- Use conditions
 - Storage temperature
-20/70 °C
- Temperature
 - Operating temperature
-5/45 °C