



4 Gang Dimmer Switch 250W Polished Brass

Technical Characteristics

Frequency	50/60 Hz
Operating voltage	240 V AC
Material	stainless steel
Type of load	inductive
Component	with 2 fixing screws M3.5 x 30 mm
Dimming principle	phase cut-on