



## KNX glass sensor 1gang comf, intg bus coupl. unit, KNX-TS sensor, glass p.white

### Technical Characteristics

Fixing mode	flush-mounting
Function	Blocking function for sensor surface e.g. for cleaning the glass surface for switch, push-button, dimmer and shutter functions
Operating voltage	21 ... 32 V DC
Depth	37.7 mm
Height	160 mm
Width	86 mm
Current consumption	12.5 mA
Colour	polarwhite
RAL colour	RAL 9010 - Pure white
Material	glass
Surface appearance	glossy
Type of surface treatment	Tampography
Inscribable, with labelling field	No
Operating temperature	45 °C -5 °C
Designation syntax: Core designation/function	Glass sensor
Application, usage	KNX - operating systems