

WPDP84FOBKO

20A Double Pole Switch with Flex Outlet & Back Box with Knockouts

Configuration

Switch mode	2pole
-------------	-------

Dimensions

Depth	53.2 mm
-------	---------

Height	86 mm
--------	-------

Width	86 mm
-------	-------

Frequency

Frequency	50;60 Hz
-----------	----------

Materials

Colour	grey
--------	------

Material	Steel
----------	-------

Installation, mounting

Imprint	with clear terminal markings
---------	------------------------------

Scope of delivery

Component with 2 fixing screws M3.5 x 20 mm and M3.5 x 30 mm each

Equipment

Lighting without lighting (cannot be illuminated)

Identification

Designation syntax: Core designation/function Switch
