

TYA624C

Output device for 4 shutters or blinds 230V~



- Architecture
 - Bus system
KNX
 - Number of blinds/shutters outputs
4
 - Fixing mode
REG
- Functions
 - Function
with safety functions e.g. for wind, rain, alarm
with positioning function for blind and lamella position
with sun shade function
- Controls and indicators
 - Indicator lamp
yes
- Connectivity
 - Bus system radio frequent
Yes
- Main electrical features
 - Type of supply voltage
AC
- Dimensions
 - Depth
65 mm
 - Height
90 mm
- Frequency

- Frequency
50/60 Hz
- Power
 - Contact rating with 230 V in AC1
1380 W
 - Total power loss under IN
2 W
- Capacity
 - Breaking capacity
6A 250V AC1
- Capacity
 - Number of modules
4
- Materials
 - Colour
light grey
 - RAL colour
RAL 7035 - Light grey
- Connection
 - Connection cross-sect. flexible conductor
0,75 / 2,5mm²
 - Connection cross-sect. rigid cable
0,75 / 2.5mm²
 - Type of connection
quick connect
 - Number of contacts
4
 - Type of connection
with QuickConnect plug-in terminals
- Settings
 - Setting
switching time on change of direction adjustable
- Safety
 - Protection index IP
IP20
- Use conditions
 - Storage temperature
-20/70 °C
- Temperature
 - Operating temperature
-5/45 °C
- Identification
 - Designation syntax: Main application
230 V
 - Designation syntax: Core designation/function
Blind actuator