

RCCB 1P+N 40A 30mA F

Technical Characteristics

Neutral position	right
Type of pole	1P+N
Fixing mode	DIN rail type O (symmetrical)
Frequency	50 Hz
Type of supply voltage	AC
Short-time delayed tripping	Yes
Quick connect	
Can be accessorized	Yes
European directive WEEE	concerned
Protection index IP	IP20
Residual current type	F