

HBD401H

Electronic earth leakage add-on block 4P 400A I_{dn} adjustable, time delay

Architecture

Number of poles	4 P
-----------------	-----

Main electrical features

Rated operational voltage U _e	220 / 415 V
--	-------------

Frequency	50;60 Hz
-----------	----------

Rated current	400 A
---------------	-------

Voltage

Rated insulation voltage	500 V
--------------------------	-------

Rated impulse withstand voltage	6000 V
---------------------------------	--------

Electric current

Rated residual operating current	30 / 100 / 300 mA / 1 / 3 / 6 A
----------------------------------	---------------------------------

Power

Total power loss under I _N	24 W
---------------------------------------	------

Tripping

Short-time delayed tripping	No
-----------------------------	----

Connection

Connection cross-sect. rigid cable	240 mm ²
------------------------------------	---------------------

Equipment

Can be accessorized	No
---------------------	----

Standards

Standard text	IEC 60947-2
---------------	-------------

European directive WEEE	concerned
-------------------------	-----------

Safety

Residual current type	A
-----------------------	---
