

# HBD631H

Electronic earth leakage add-on block 4P 500A I<sub>dn</sub> adjustable, time delay

## Architecture

Number of poles	4 P
-----------------	-----

## Main electrical features

Rated operational voltage U <sub>e</sub>	220 / 415 V
--	-------------

Frequency	50;60 Hz
-----------	----------

Rated current	500 A
---------------	-------

## Voltage

Rated insulation voltage	500 V
--------------------------	-------

Rated impulse withstand voltage	6000 V
---------------------------------	--------

## Electric current

Rated residual operating current	30 / 100 / 300 mA / 1 / 3 / 6 A
----------------------------------	---------------------------------

## Power

Total power loss under I <sub>N</sub>	24 W
---------------------------------------	------

## Tripping

Short-time delayed tripping	No
-----------------------------	----

---

Connection

Connection cross-sect. rigid cable	240 mm <sup>2</sup>
------------------------------------	---------------------

---

Equipment

Can be accessorized	No
---------------------	----

---

Standards

Standard text	IEC 60947-2
---------------	-------------

---

European directive WEEE	concerned
-------------------------	-----------

---

Safety

Residual current type	A
-----------------------	---

---