



75162599

IP20

B.IQ push-button 2gang comf, KNX - B.IQ, p. white, matt, plastic

Technical characteristics

Architecture

| | |
|-------------|----------------|
| Fixing mode | flush-mounting |
|-------------|----------------|

Functions

| | |
|----------|---|
| Function | for switch, push-button, dimmer and shutter functions |
|----------|---|

Dimensions

| | |
|--------|---------|
| Height | 88.5 mm |
|--------|---------|

| | |
|-------|---------|
| Width | 88.5 mm |
|-------|---------|

Materials

| | |
|--------|------------|
| Colour | polarwhite |
|--------|------------|

| | |
|------------|-----------------------|
| RAL colour | RAL 9010 - Pure white |
|------------|-----------------------|

| | |
|----------|---------------|
| Material | thermoplastic |
|----------|---------------|

| | |
|--------------------|------|
| Surface appearance | matt |
|--------------------|------|

| | |
|---------------------------|-----------|
| Type of surface treatment | untreated |
|---------------------------|-----------|

Accessories included

| | |
|-----------------------------------|----|
| Inscribable, with labelling field | No |
|-----------------------------------|----|

Safety

| | |
|---------------------|------|
| Protection index IP | IP20 |
|---------------------|------|

| | |
|------------|-----------------------------|
| Protection | with dismantling protection |
|------------|-----------------------------|

Use conditions

| | |
|-----------------------|------------|
| Operating temperature | -5...45 °C |
|-----------------------|------------|