



75642135



KNX glass sensor 2g thermostat, display, intg bus coupl. , KNX-TS sensor, bl.

Technical characteristics

Architecture

Fixing mode flush-mounting

Functions

Function with valve protection function ; for switch, push-button, dimmer, blind and thermostat functions

Dimensions

Depth 37.7 mm

Height 160 mm

Width 86 mm

Power

Current consumption 23 mA

Materials

Colour black

RAL colour RAL 9005 - Jet black

Material glass

Surface appearance glossy

Type of surface treatment Tampography

Accessories included

Inscribable, with labelling field No

Safety

Protection index IP IP20

Use conditions

Operating temperature -5...45 °C