



### Analogie voltmeter 0-500V

#### Technical Characteristics

|   |                         |
|---|-------------------------|
| Fixing mode                               | Din-Rail                |
| Frequency                                 | 45/65 Hz                |
| Rated insulation voltage                  | 2000 V                  |
| Depth of installed product                | 54 mm                   |
| Height of installed product               | 90 mm                   |
| Width of installed product                | 70 mm                   |
| Power consumed                            | 3 VA                    |
| Total power loss under IN                 | 3.5 W                   |
| Type of measuring instrument              | voltmeter               |
| Number of modules                         | 4                       |
| Mounting type                             | din-Rail                |
| Connection cross-sect. flexible conductor | 1 / 6mm <sup>2</sup>    |
| Connection cross-sect. rigid cable        | 1,5 / 10mm <sup>2</sup> |
| Type of connection                        | with screw              |
| Protection index IP                       | IP20                    |
| Operating temperature                     | 25 °C<br>50 °C          |