

Product data sheet

WRPS16PBB

:hager



Intermediate Switch Polished Brass Black Insert

Technical Characteristics

Switch mode	intermediate
Frequency	50/60 Hz
Rated current	20 A
Depth	24 mm
Height	86 mm
Width	86 mm
Colour	brass optics
Material	stainless steel
Imprint	with clear terminal markings
Component	with 2 fixing screws M3.5 x 30 mm
Lighting	without lighting (cannot be illuminated)
Insert	insert, black
Designation syntax: Core designation/function	Intermediate switch