

WMSSU83/FAN

13A FCU Switched Marked FAN

Configuration

Switch mode 2pole

Main electrical features

Rated current 13 A

Fuse

Fuse with ceramic fine fuse F 13A

Dimensions

Depth 30.3 mm

Height 86 mm

Width 86 mm

Frequency

Frequency 50;60 Hz

Materials

Colour white

Material	Urea-formaldehyde
-----------------	-------------------

Installation, mounting

Imprint	with clear terminal markings
----------------	------------------------------

Cable

Wiring	with double earth connection
---------------	------------------------------

Scope of delivery

Component	with 2 fixing screws M3.5 x 30 mm
------------------	-----------------------------------

Equipment

Lighting	without lighting (cannot be illuminated)
-----------------	--

Standards

Standard	BS 1363-4
-----------------	-----------

Safety

Protection	to protect downstream loads
-------------------	-----------------------------
