



Neutral connecting block 125A

Technical Characteristics

Number of poles	1 P
Type of pole	N
Fixing mode	DIN rail type O (symmetrical)
Rated operational voltage Ue	230 V 400 V
Rated current	125 A
Type of supply voltage	AC
Rated insulation voltage	440 V
Rated impulse withstand voltage	4 kV
Depth of installed product	60 mm
Height of installed product	83 mm
Width of installed product	17.5 mm
Number of modules	1
Tightening torque	3,6Nm
European directive WEEE	concerned
Protection index IP	IP20
Operating temperature	-20 °C 50 °C