



Latching 2NC Pushbutton

Technical Characteristics

Rated operational voltage Ue	230 V
Frequency	50/60 Hz
Rated current	16 A
Rated insulation voltage	250 V
Rated impulse withstand voltage	4000 V
Depth of installed product	66 mm
Height of installed product	83 mm
Width of installed product	17.5 mm
Electric endurance in number of cycles	15000
Number of mechanical operations	15000
Number of modules	1
Colour	not applicable
Tightening torque	1,7Nm
Connection cross-sect. flexible conductor	0,75 / 6mm ²
Connection cross-sect. rigid cable	0,75 / 10mm ²
Type of connection	with screw
Can be accessorized	No
European directive WEEE	concerned
Protection index IP	IP20
Operating temperature	-20 °C 50 °C