




80144329



Push-button 4gang, + RGB LED, internal temp. sensor, KNX - Q.1/Q.3, p. white

Technical characteristics

Architecture

Fixing mode flush-mounting

Dimensions

Height 58.7 mm

Width 58.7 mm

Power

Power consumption, KNX ≈ 150 mW

Materials

Colour polarwhite

RAL colour RAL 9010 - Pure white

Material thermoplastic

Surface appearance velvety

Type of surface treatment Painted

Accessories included

Inscribable, with labelling field Yes

Safety

Protection index IP IP20

Protection with dismantling protection

Use conditions

Operating temperature -5...45 °C