



80144329



**Push-button 4gang, + RGB LED, internal temp. sensor, KNX - Q.1/Q.3, p. white**

### Technical Characteristics

Fixing mode	flush-mounting
Function	Function for manual interruption of automatic functions already triggered
Height	58.7 mm
Width	58.7 mm
Power consumption, KNX	≈ 150 mW
Colour	polarwhite
RAL colour	RAL 9010 - Pure white
Material	thermoplastic
Surface appearance	velvety
Type of surface treatment	Painted
Inscribable, with labelling field	Yes
Protection index IP	IP20
Protection	with dismantling protection
Operating temperature	-5...45 °C
Designation syntax: Core designation/function	Push-button
Application, usage	KNX - operating systems