




80162780

IP20



Push-button 2gang, RGB LED, int. temp. sensor, KNX - S.1/B.3/B.7, f. p.white

Technical characteristics

Architecture

Fixing mode flush-mounting

Dimensions

Height 55.3 mm

Width 55.8 mm

Power

Power consumption, KNX ≈ 150 mW

Materials

Colour white/polarwhite

RAL colour RAL 1013 - Oyster white

Material thermoplastic

Surface appearance matt

Type of surface treatment untreated

Accessories included

Inscribable, with labelling field Yes

Safety

Protection index IP IP20

Protection with dismantling protection

Use conditions

Operating temperature -5...45 °C