


80163770



IP20



Push-button 3gang, lab. field, RGB LED, int. temp. sensor, KNX - K.1, p.white

Technical Characteristics

Architecture

Fixing mode flush-mounting

Functions

Function Function for manual interruption of automatic functions already triggered

Dimensions

Height 55.1 mm

Width 70.9 mm

Power

Power consumption, KNX ≈ 150 mW

Materials

Colour polarwhite

RAL colour RAL 9010 - Pure white

Material thermoplastic

Surface appearance matt

Type of surface treatment untreated

Accessories included

Inscribable, with labelling field Yes

Safety

Protection index IP IP20

Protection with dismantling protection

Use conditions

Operating temperature -5...45 °C

Identification

Designation syntax: Core designation/function Push-button

Application, usage KNX - operating systems