




80163780



Push-button 3g, lab. field,RGB LED, int. temp.sensor, KNX-S.1/B.3/B.7,f.wh.p.wh.

Technical characteristics

Architecture

Fixing mode flush-mounting

Functions

Function Function for manual interruption of automatic functions already triggered

Dimensions

Height 55.3 mm

Width 55.8 mm

Power

Power consumption, KNX ≈ 150 mW

Materials

Colour white/polarwhite

RAL colour RAL 1013 - Oyster white

Material thermoplastic

Surface appearance glossy

Type of surface treatment untreated

Accessories included

Inscribable, with labelling field Yes

Safety

Protection index IP IP20

Protection with dismantling protection

Use conditions

Operating temperature -5...45 °C