





80164770



**IP20**



**Push-button 4gang, lab. field, + RGB LED, int. temp. sensor, KNX - K.1, p.white**

**Technical Characteristics**

Fixing mode	flush-mounting
Function	Function for manual interruption of automatic functions already triggered
Height	55.1 mm
Width	70.9 mm
Power consumption, KNX	≈ 150 mW
Colour	polarwhite
RAL colour	RAL 9010 - Pure white
Material	thermoplastic
Surface appearance	matt
Type of surface treatment	untreated
Inscribable, with labelling field	Yes
Protection index IP	IP20
Protection	with dismantling protection
Operating temperature	-5...45 °C
Designation syntax: Core designation/function	Push-button
Application, usage	KNX - operating systems