





80164773



IP20



Push-button 4gang, lab. field, +RGB LED, int. temp. sensor, KNX-K.5, stainl.steel

Technical characteristics

Architecture

Fixing mode flush-mounting

Dimensions

Height 55.1 mm

Width 70.9 mm

Power

Power consumption, KNX ≈ 150 mW

Materials

Colour stainless steel

RAL colour RAL 9022 - Pearl light grey

Material thermoplastic

Surface appearance matt

Type of surface treatment Painted

Accessories included

Inscribable, with labelling field Yes

Safety

Protection index IP IP20

Protection with dismantling protection

Use conditions

Operating temperature -5...45 °C