



80164773



IP20



## Push-button 4gang, lab. field, +RGB LED, int. temp. sensor, KNX-K.5, stainl.steel

### Technical characteristics

#### Architecture

Fixing mode flush-mounting

#### Functions

Function Function for manual interruption of automatic functions already triggered

#### Dimensions

Height 55.1 mm

Width 70.9 mm

#### Power

Power consumption, KNX ≈ 150 mW

#### Materials

Colour stainless steel

RAL colour RAL 9022 - Pearl light grey

Material thermoplastic

Surface appearance matt

Type of surface treatment Painted

#### Accessories included

Inscribable, with labelling field Yes

#### Safety

Protection index IP IP20

Protection with dismantling protection

#### Use conditions

Operating temperature -5...45 °C