





80164773



IP20



Push-button 4gang, lab. field, +RGB LED, int. temp. sensor, KNX-K.5, stainl.steel

Technical characteristics

Architecture

Fixing mode flush-mounting

Dimensions

Height 55.1 mm

Width 70.9 mm

Power

Power consumption, KNX ≈ 150 mW

Materials

Colour stainless steel

RAL colour RAL 9022 - Pearl light grey

Material thermoplastic

Surface appearance matt

Type of surface treatment Painted

Accessories included

Inscribable, with labelling field Yes

Safety

Protection index IP IP20

Use conditions

Operating temperature -5...45 °C