




80164774



IP20



**Push-button 4gang, lab. field, + RGB LED, internal temp. sensor, KNX - K.5, al.**

#### Technical characteristics

##### Architecture

Fixing mode flush-mounting

##### Dimensions

Height 25 mm

Width 66.8 mm

##### Power

Power consumption, KNX  $\approx$  150 mW

##### Materials

Material thermoplastic

##### Accessories included

Inscribable, with labelling field Yes

##### Safety

Protection index IP IP20

Protection with dismantling protection

##### Use conditions

Operating temperature -5...45 °C