




80164776



IP20



Push-button 4gang, lab. field, + RGB LED, internal temp. sensor, KNX - K.1, ant.

Technical characteristics

Architecture

Fixing mode flush-mounting

Dimensions

Height 25 mm

Width 66.8 mm

Power

Power consumption, KNX ≈ 150 mW

Materials

Material thermoplastic

Accessories included

Inscribable, with labelling field Yes

Safety

Protection index IP IP20

Protection with dismantling protection

Use conditions

Operating temperature -5...45 °C