






80164780

IP20



Push-button 4g, lab. field,RGB LED, int. temp.sensor, KNX-S.1/B.3/B.7,f.wh.p.wh.

#### Technical characteristics

#### Functions

Function	Function for manual interruption of automatic functions already triggered
----------	---

#### Dimensions

Height	55.3 mm
Width	55.8 mm

#### Power

Power consumption, KNX	≈ 150 mW
------------------------	----------

#### Materials

Surface appearance	glossy
Type of surface treatment	untreated

#### Accessories included

Inscribable, with labelling field	Yes
-----------------------------------	-----

#### Safety

Protection	with dismantling protection
------------	-----------------------------

#### Use conditions

Operating temperature	-5...45 °C
-----------------------	------------