




80164780



Push-button 4g, lab. field,RGB LED, int. temp.sensor, KNX-S.1/B.3/B.7,f.wh.p.wh.

Technical characteristics

Architecture

Fixing mode flush-mounting

Dimensions

Height 55.3 mm

Width 55.8 mm

Power

Power consumption, KNX ≈ 150 mW

Materials

Colour white/polarwhite

RAL colour RAL 1013 - Oyster white

Material thermoplastic

Type of surface treatment untreated

Accessories included

Inscribable, with labelling field Yes

Safety

Protection index IP IP20

Protection with dismantling protection

Use conditions

Operating temperature -5...45 °C