



80164785



IP20



**Push-button 4g, lab. field,RGB LED, int. temp.sensor, KNX-S.1/B.3/B.7, f.ant.al.**

#### Technical characteristics

##### Architecture

Fixing mode flush-mounting

##### Dimensions

Height 55.3 mm

Width 55.8 mm

##### Power

Power consumption, KNX  $\approx$  150 mW

##### Materials

Colour aluminium/anthracite

RAL colour RAL 7016 - Anthracite grey

Material thermoplastic

Type of surface treatment untreated

##### Accessories included

Inscribable, with labelling field Yes

##### Safety

Protection index IP IP20

Protection with dismantling protection

##### Use conditions

Operating temperature -5...45 °C